


## Laser for hair removal HR-1200-808DS



### Stand-alone one-handle 808 nm diode laser

Gold standard for hair removal, suitable for all hair types and skin colors, including tanned

Handle power 1,200 W

+421 353 211 408

[fitaims.com](http://fitaims.com)

[info@fitaims.com](mailto:info@fitaims.com)



Diode laser treats unwanted hair by selectively heating and destroying the melanin in the hair follicles, and thus interrupting the hair growth. By targeting the specific areas in the skin the laser does not damage the surrounding tissue.

808 nm diode laser is the most professional hair removal device as it is:

- **Safe and comfortable.** High melanin absorption rate and ultra-short pulse make the treatment less painful. Advanced sapphire cooling system protect the skin from overheating.
- Suitable for treatment of almost **all skin types** including tanned and dark skin.
- Has a certain **skin rejuvenation "side-effect"**. Promotes collagen production and thus improves skin condition.

2


You may opt for one of two standard handles



smaller spot size  
for face, chin,  
lips, hairline,  
forehead




larger spot size for larger  
treatment areas like  
bikinis, thighs, calves,  
upper limbs, underarms



- Frequency adjustment
- Pulse width adjustment
- Energy adjustment
- Real-time temperature monitoring

3

## Highlights



**high customization**  
suitable for almost all  
skin-hair profiles



**efficiency**  
high output power ensures  
fast and stable result



**large screen size**  
12.1" and mini 1.54" handle  
screen make operator's  
work convenient and fast



**easy operation**  
intelligent software with  
preset parameters for  
all skin types




**long service life**  
guaranteed 100,000,000  
shots - long-lasting and  
seamless machine operation



**TEC cooling system**  
comfortable treatment &  
12-hour downtime-free  
machine operation

4



Temperature sensor position  
Temperature sensor is installed in the handle.  
The surface temperature is monitored in real  
time and displayed on the screen.

Sapphire crystal  
The sapphire glass provides effective  
treatment area cooling (up to -30°C) to  
make the hair removal process safer.

Super refrigeration system  
Two semiconductor cooling plates,  
108 W super cooling power, the  
surface temperature of the spot  
can reach -30°C.

Customer's eye protector  
Operator's goggles

5,000 EUR 400 EUR 6 EUR 100 EUR

5

## Accessories

1,200 W handle (12x20 mm)

5,000 EUR

Face tip (only for 12x20 mm handle)

400 EUR

Customer's eye protector

6 EUR

Operator's goggles

100 EUR

6

## Warranty

2 year warranty for spare parts.

During the first year of warranty,  
spare parts and delivery are free of  
charge. During the second year, only  
spares are free of charge, the delivery  
should be covered by the customer.

## Downtime

12 hours of continuous  
work guaranteed

## Servicing / Maintenance

Generally the machine is maintenance-free.

Keep the handles clean to ensure hygiene.

There may be a need to refill water in a water cooling  
tank approximately once per 6 months, the corresponding  
warning will appear on the machine screen.



7

## Specifications

Wavelength	808 nm
Pulse width	1-200 msec

Energy density	1-120 J/cm <sup>2</sup> (deviation ≤±2%)
----------------	--

Handle power	1,200 W
--------------	---------

Frequency	1-10 Hz
-----------	---------

Spot size	12*12 mm (12*20 mm optional)
-----------	---------------------------------

Power requirements	220 V±10% 10 A 50 Hz 110 V±10% 10 A 60 Hz
--------------------	--

Power consumption	3,000 W
-------------------	---------

Dimensions	Package size	Net weight
------------	--------------	------------

512x541x1303 mm	630 x 690 x 1210 mm	54 kg
-----------------	---------------------	-------



7